


# 120 Belmont Drive Somerset, NJ 08873-1204

american fibertek

Phone: 732.302.0660 Fax: 732.302.0667



Instruction Manual

RT-980C-SL Eight Channel Video Transmitter



# **CAUTION**

RISK OF ELECTRIC SHOCK DO NOT OPEN



CAUTION: TO REDUCE THE RISK OF ELECTRIC SHOCK:

DO NOT EXPOSE THIS PRODUCT TO RAIN OR MOISTURE
DO NOT REMOVE COVER OR BACK
NO USER-SERVICEABLE PARTS INSIDE
REFER SERVICING TO QUALIFIED SERVICE PERSONNEL

This unit complies with 21 CFR 1040.10 and 1040.11

# INSTALLATION AND OPERATION INSTRUCTIONS

#### INTRODUCTION

Thank you for purchasing your American Fibertek RT-980C-SL singlemode eight channel video transmitter. Please take a few minutes to read these installation instructions in order to obtain the maximum performance from this product.

## **FUNCTIONAL DESCRIPTION**

The RT-980C-SL operates as half of a transmitter / receiver pair for the transmission of eight channels of high performance digital NTSC, PAL, RS170, or RS343 video signals. The RT-980C-SL is designed to operate with the MR or RR-980C-SL video receiver over one singlemode fiber optic cable. Refer to the data sheets for detailed performance specifications.

#### **INSTALLATION**

THE INSTALLATION OF THIS UNIT SHOULD BE MADE BY A QUALIFIED SERVICE PERSON(S) AND MUST CONFORM TO ALL LOCAL CODES.

#### **POWER SOURCE**

Power to the unit is supplied by the sub-rack. Please refer to the SR-20/2 and PSR-2 instructions for further details.

#### POWER CONNECTION

Power is supplied to the unit via four finger backplane connectors. The RR-980C-SL can be inserted into the sub-rack or removed from the sub-rack with power applied to the backplane.

#### FIBER CONNECTION


The fiber optic connection is made via a ST/PC connector located on the right side of the unit. Be sure to allow sufficient room for the required minimum bend radius of the fiber cable used.

#### **VIDEO INPUT CONNECTIONS**

The video input connections are made via BNC connectors on the right side of the unit. The video input should be connected to an appropriate  $75\Omega$  baseband video source such as a camera or a video recorder output. For optimum performance the video cables should be the shortest length of coax practical

## RT-980C-SL STATUS INDICATORS

The RT-980C-SL transmitter provides the LED status indicators to aid in installation and troubleshooting:



#### VIDEO 1 THROUGH VIDEO 8

A bi-color LED indicator is provided for each of the eight video inputs of the RT-980C-SL. DC power and video status associated with each of these LED's are summarized below.

Video Presence LED	DC Power Status	Video Status
Green	On	Proper Input Video Present
Red	On	Input Video Not Detected
Off	Off	Check Power Supply

#### LIFETIME WARRANTY INFORMATION

American Fibertek, Inc warrants that at the time of delivery the products delivered will be free of defects in materials and workmanship. Defective products will be repaired or replaced at the exclusive option of American Fibertek. A Return Material Authorization (RMA) number is required to send the products back in case of return. All returns must be shipped prepaid. This warranty is void if the products have been tampered with. This warranty shall be construed in accordance with New Jersey law and the courts of New Jersey shall have exclusive jurisdiction over this contract. **EXCEPT FOR THE FOREGOING WARRANTY, THERE IS NO WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR OTHERWISE, EXPRESSED OR IMPLIED, WHICH EXTENDS BEYOND THE WARRANTY SET FORTH IN THIS AGREEMENT.** In any event, American Fibertek will not be responsible or liable for contingent, consequential, or incidental damages. No agreement or understanding, expressed or implied, except as set forth in this warranty, will be binding upon American Fibertek unless in writing, signed by a duly authorized officer of American Fibertek.

# **SERVICE** INFORMATION

There are no user serviceable parts inside the unit. In the event that service is required to this unit, please direct all inquiries to:

 American Fibertek, Inc.
 Phone: (877) 234-7200

 120 Belmont Drive
 Phone: (732) 302-0660

 Somerset, NJ 08873
 FAX (732) 302-0667

E-mail: techinfo@americanfibertek.com